

**SCREWTY M8 KO O. SD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The Screwty® attachment is suitable for M8 round plug-in connectors, with an outside dimension of the knurled nut of  $10 \pm 0.3$  mm. The tightening torque is 0.5-0.6 Nm.

**General ordering data**

Version	Cable gland tool adapter for moulded M8 lines
Order No.	<a href="#">1900110000</a>
Type	SCREWTY M8 KO O. SD
GTIN (EAN)	4032248409969
Qty.	1 items
Packaging	Plastic bag

## SCREWTY M8 KO O. SD

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Net weight	11.44 g
------------	---------

### Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

### Screwing tools

Connection thread	M8	Size	10 mm
-------------------	----	------	-------

### Classifications

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		