

SCREWTY M8 KO O. SD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The Screwty® attachment is suitable for M8 round plug-in connectors, with an outside dimension of the knurled nut of 10 ± 0.3 mm. The tightening torque is 0.5-0.6 Nm.

General ordering data

Version	Cable gland tool adapter for moulded M8 lines
Order No.	1900110000
Type	SCREWTY M8 KO O. SD
GTIN (EAN)	4032248409969
Qty.	1 items
Packaging	Plastic bag

SCREWTY M8 KO O. SD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	11.44 g
------------	---------

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Screwing tools

Connection thread	M8	Size	10 mm
-------------------	----	------	-------

Classifications

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		