Data sheet

SCREWTY M12F KO O. SD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The Screwty® attachment is suitable for customisable M12 round plug-in connectors, with an outside dimension of the knurled nut of 19.8 ±0.3 mm. The tightening torque is 0.8-1.2 Nm.

General ordering data

Version	Cable gland tool adapter for M12 connectors
Order No.	1900120000
Type	SCREWTY M12F KO O. SD
GTIN (EAN)	4032248409976
Qty.	1 items
Packaging	Plastic bag

SCREWTY M12F KO O. SD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	17.8 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Screwing tools

Connection thread	M12	Size	19.8 mm

Classifications

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-01-90-90
ECLASS 15.0	21-01-90-90		