



We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

### General ordering data

Version	Z-series, Accessories, yellow, 5.1 mm
Order No.	<a href="#">1908560000</a>
Type	BA RC ZPS2.5
GTIN (EAN)	4032248534241
Qty.	25 items

## BA RC ZPS2.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	12.77 mm	Depth (inches)	0.5028 inch
Height	23.45 mm	Height (inches)	0.9232 inch
Width	5.1 mm	Width (inches)	0.2008 inch
Net weight	0.52 g		

### Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-50 °C...75 °C
Operating temperature	-50 °C...	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Material data

Basic material	Wemid	Insulating material	Wemid
Colour	yellow	UL 94 flammability rating	V-0

### System specifications

Version	For the terminals
---------	-------------------

### Additional technical data

Type of fixing	Plugged	Installation advice	Direct mounting
----------------	---------	---------------------	-----------------

### Conductors for clamping (rated connection)

Type of connection	without
--------------------	---------

### Dimensions

Pitch in mm (P)	5.10 mm
-----------------	---------

### General

Installation advice	Direct mounting
---------------------	-----------------

### Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		