

VG M63-K67**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG K (standard plastic cable gland), Cable glands, straight, M 63, 18 mm, OD min. 34 - OD max. 44 mm, Polyamide 6
Order No.	1909750000
Type	VG M63-K67
GTIN (EAN)	4032248536672
Qty.	10 items

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Height	53 mm	Height (inches)	2.0866 inch
Length	71 mm	Length (inches)	2.7953 inch
Net weight	100.1 g		

Temperatures

Operating temperature -20 °C...80 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General information

Outer cable diameter, max.	44 mm	Outer cable diameter, min.	34 mm
Tightening torque	12 Nm	Silicone	No
UL 94 flammability rating	V-2	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Pitch of thread	1.5 mm
Halogen	No	Standards	EN/IEC 62444
AF size 1	65 mm	Protection degree	IP67
Cable gland	metric	Basic material	Polyamide 6
Seal insert	NBR	External thread	M 63
Length of thread	18 mm	Torque for cap nut, max.	20.50 Nm
Torque for lock nut, min.	11.50 Nm	Torque for connecting adapter, max.	12.50 Nm
Torque for connecting adapter, min.	11.50 Nm	Torque for cap nut, min.	19.50 Nm
Torque for lock nut, max.	12.50 Nm		

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-01
ECLASS 15.0	27-14-08-01		

VG M63-K67

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Plastic lock nuts, grey



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M63 - K GR	Version	
Order No.	1772510000	SKMU PA (plastic locknut), Locknut, M 63, 8 mm, Polyamid 6 (PA6 -	
GTIN (EAN)	4032248130252	GF30)	
Qty.	10 ST		

Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M63-NP	Version	
Order No.	1736290000	GWDR NP (flat gasket - neoprene), Sealing ring, M 63, Neoprene	
GTIN (EAN)	4008190956080		
Qty.	10 ST		

Polyethylene flat gasket - GWDR PO



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	GWDR M63-PO	Version	
Order No.	1777990000	GWDR PO (flat gasket - polyethylene), Sealing ring, M 63,	
GTIN (EAN)	4032248158256	Polyethylene	
Qty.	50 ST		