

CLI C 3-30 SDR SG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|--|
| Version | CableLine, Conductor and cable markers, 8 - 16 mm, 30 x 11 mm, To customer specification |
| Order No. | 1912790000 |
| Type | CLI C 3-30 SDR SG |
| GTIN (EAN) | 4032248542635 |
| Qty. | 100 items |

CLI C 3-30 SDR SG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 17 mm | Depth (inches) | 0.6693 inch |
| Height | 30 mm | Height (inches) | 1.1811 inch |
| Width | 11 mm | Width (inches) | 0.4331 inch |
| Net weight | 3.75 g | | |

Temperatures

Operating temperature range -30...60 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

| | | | |
|-----------------------------------|----------------------------|-----------------------------------|---------------------------|
| Orientation of print | horizontal | Type of printing | To customer specification |
| Printing method | Ink jet technology | Version | Loop |
| Width | 11 mm | UL 94 flammability rating | V-0 |
| Operating temperature range, max. | 60 °C | Operating temperature range, min. | -30 °C |
| Colour | To customer specification | Halogen | Yes |
| Basic material | PVC, soft, without Cadmium | Colour of printing | black |
| Printed characters | To customer specification | Operating temperature range | -30...60 °C |
| Imprint | Custom printing | | |

Conductor and cable markers

| | | | |
|----------------------------------|-------------------------|-------------------------------|--------------------|
| Halogen | Yes | Conductor cross-section, max. | 70 mm ² |
| Conductor cross-section, min. | 16 mm ² | Conductor O.D., max. | 16 mm |
| Conductor O.D., min. | 8 mm | Conductor O.D. | 8 - 16 mm |
| Cross-section for connected wire | 16 - 70 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

Drawings



Similar to illustration