


**ESG 5/10 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |  |
|------------|--|
| Version    | ESG, Device markers x 10 mm, PA 66, Colour: white, pluggable |
| Order No.  | <a href="#">1919940000</a>                                   |
| Type       | ESG 5/10 MC NE WS  |
| GTIN (EAN) | 4032248557714  |
| Qty.       | 400 items  |

**ESG 5/10 MC NE WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 0.8 mm | Depth (inches)  | 0.0315 inch |
| Height     | 5 mm   | Height (inches) | 0.1968 inch |
| Width      | 10 mm  | Width (inches)  | 0.3937 inch |
| Net weight | 0.2 g  |                 |             |

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.001 kg CO2 eq. |  |

**General data**

|  |   |           |  |
|--|---|-----------|--|
| Material colour according to resistance code | 9   |           |  |
| Version                                      | pluggable   |           |  |
| Width  | 10 mm   |           |  |
| UL 94 flammability rating                    | V-2   |           |  |
| Operating temperature range, max.            | 100 °C  |           |  |
| Operating temperature range, min.            | -40 °C  |           |  |
| Colour                                       | white   |           |  |
| Halogen                                      | No  |           |  |
| Basic material                               | PA 66   |           |  |
| Printed characters                           | without   |           |  |
| Number of markers per packaging unit         | Form of supply  | MultiCard |  |
| compatible printer                           | <a href="#">PRINTJET CONNECT, MCP BASIC 2, MCP PLUS 2</a> |           |  |
| Number of markers per combination            | 1 MultiCard = Device markers                              |           |  |
| Operating temperature range                  | -40...100 °C  |           |  |
| Application/manufacturer                     | Beckhoff, Turck, SAI distributor                          |           |  |

**Device markers**

Halogen No

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ETIM 10.0   | EC001288    | ECLASS 14.0 | 27-28-11-04 |
| ECLASS 15.0 | 27-28-11-04 |             |             |

**Drawings**

