


CC-H 30/60

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	ClipCard, Accessories, 30 x 60 mm, black
Order No.	1934430000
Type	CC-H 30/60
GTIN (EAN)	4032248590995
Qty.	10 items

CC-H 30/60

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	5.5 mm	Depth (inches)	0.2165 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	60 mm	Width (inches)	2.3622 inch
Length	60 mm	Length (inches)	2.3622 inch
Diameter	0 mm	Net weight	5 g

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.038 kg CO2 eq.	

General data

Version	Marker holder		
Width	60 mm		
UL 94 flammability rating	V-2		
Operating temperature range, max.	100 °C		
Operating temperature range, min.	-40 °C		
Colour	black		
Halogen	No		
Length	60 mm		
Basic material	Polyamide 66		
Number of markers per packaging unit	Form of supply	MultiCard	
Recommended industries	Machinery		
Number of markers per combination	1 MultiCard = Accessories		
Operating temperature range	-40...100 °C		

Device markers

Diameter	0 mm	Halogen	No
----------	------	---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

