Data sheet

STB 21.6/45 SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

General ordering data

Version	Socket (terminal), Plug-in depth: 11.1 mm, 0.00 mm, Depth: 45 mm
Order No.	1936270000
Type	STB 21.6/45 SW
GTIN (EAN)	4032248606009
Qty.	50 items

Data sheet

STB 21.6/45 SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	45 mm	Depth (inches)	1.7716 inch
Height	6.1 mm	Height (inches)	0.2402 inch
Width	6.1 mm	Width (inches)	0.2402 inch
Net weight	3.34 g		

Temperatures

Ambient temperature	-60 °C...85 °C	Continuous operating temperature, min.	-50 °C
Continuous operating temperature, max.	120 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	dce63e23-eea1-4eaa-9071-1c98fc8fa2ea

Material data

Basic material	Wemid	Colour	black
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals

Additional technical data

Type of fixing	when screwed in	Installation advice	Direct mounting
Type of mounting	when screwed in		

Dimensions

Metric size of the thread, external	0.00 mm	Plug-in depth	11.1 mm
TS 35 offset	45.5 mm		

General

Installation advice	Direct mounting	Operating temperature range, max.	100 °C

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		