

## DP VWGK 4 GY BX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Integrate, expand and customise: the perfect supplement to every application. Universal system accessories enable easy adaptation of the interfaces to fulfil specific requirements for the relevant application.

### General ordering data

Version	OMNIMATE Power - series WGK, Feed-through terminal
Order No.	<a href="#">1936430000</a>
Type	DP VWGK 4 GY BX
GTIN (EAN)	4032248758982
Qty.	50 items
Product data	UL:

## DP VWGK 4 GY BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	20.5 mm	Height (inches)	0.8071 inch
Width	4 mm	Width (inches)	0.1575 inch
Length	11.4 mm	Length (inches)	0.4488 inch
Net weight	0.6 g		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### System parameters

Product family	OMNIMATE Power - series WGK
----------------	--------------------------------

### Material data

Insulating material	Wemid (PA)	Colour	grey
Colour chart (similar)	RAL 7035	Moisture Level (MSL)	
UL 94 flammability rating	V-0	Contact material	Cu-alloy
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C
Operating temperature, min.	-50 °C	Operating temperature, max.	120 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	120 °C

### Conductors suitable for connection

Reference text	Length of ferrules is to be chosen depending on the product and the rated voltage. The outside diameter of the plastic collar should not be larger than the pitch (P)
----------------	---

### Rated data acc. to IEC

tested acc. to standard	IEC 60664-1
-------------------------	-------------

### Packing

VPE length	101.00 mm	VPE width	89.00 mm
VPE height	15.00 mm		

### Important note

Notes	<ul style="list-style-type: none"> <li>Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months</li> </ul>
-------	--

### Classifications

ETIM 8.0	EC000886	ETIM 9.0	EC000886
ETIM 10.0	EC000886	ECLASS 14.0	27-25-03-01

**Technical data**

---

ECLASS 15.0

27-25-03-01

---