

SAI-AU M12 SB 4AO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The trend from IP 20 to IP 67, or rather from machines with cabinets to ones without, reaches its zenith in the IP 67 I/O slaves. In these Plug & Play solutions, the connection of individual conductors is avoided completely. This results in a substantial time-saving and eliminates mistakes in the connection of individual conductors. Today, IP 67 bus modules represent the most modern solution for the connection of sensors and actuators with the best cost-saving potential.

General ordering data

Version	SAI Active, Subbus
Order No.	1938700000
Type	SAI-AU M12 SB 4AO
GTIN (EAN)	4032248612680
Qty.	1 items

SAI-AU M12 SB 4AO

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

Dimensions and weights

Net weight 273 g

Temperatures

Storage temperature

Operating temperature

Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c, 7a, 7cl

REACH SVHC Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3

SCIP 30ca4bfe-b33c-43ed-b218-3746bc09f6a6

Connections

Connection to Subbus (SUB-IN) 1 x M8 plug 4-pole, A-coded

Connection to Subbus (SUB-OUT) 1 x M8 female 4-pole, A-coded

I/O connections 4 x M12 female, 5-pole A-coded

Digital inputs

Diagnosis indication red

Digital outputs

Diagnosis indication red

General data

Certificate CE, cULus Earth < 200 g

Supply voltage

Reverse polarity protection Yes Limits 18 V DC ... 30 V DC

Classifications

ETIM 8.0 EC001596 ETIM 9.0 EC001596

ETIM 10.0 EC001596 ECLASS 14.0 27-24-26-01

ECLASS 15.0 27-24-26-01