

## IE-PH-V04P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



PushPull plug-in connector according to IEC  
61076-3-106 ver.4 (IEC24702), plastic, empty housing

### General ordering data

Version	Empty enclosure, Plug housing, Variant 4 to IEC 61076-3-106, IP67
Order No.	<a href="#">1962520000</a>
Type	IE-PH-V04P
GTIN (EAN)	4032248644650
Qty.	10 items

## IE-PH-V04P

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

### Dimensions and weights

Depth	60.2 mm	Depth (inches)	2.3701 inch
Height	20.1 mm	Height (inches)	0.7913 inch
Width	21.2 mm	Width (inches)	0.8346 inch
Net weight	12.8 g		

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### General data

Colour	Miscellaneous	Housing main material	PA UL 94 V0
Protection degree	IP67	Plugging cycles	750

### General standards

Connector standard	IEC 61076-3-106 Var. 4	Certificate no. (cULus)	E316369
--------------------	------------------------	-------------------------	---------

### Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

**Drawings**

**Dimensioned drawing**

