Data sheet

IE-BI-SCRJ2SC-SM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



FO SC inserts for plug-in connectors ver.1 / 4 / 14

General ordering data

Version	SC insert, Bulkhead insert SCRJ to 2 SC, single-mode
Order No.	1962870000
Type	IE-BI-SCRJ2SC-SM-C
GTIN (EAN)	4032248645060
Qty.	10 items

Data sheet

IE-BI-SCRJ2SC-SM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Depth	34 mm	Depth (inches)	1.3386 inch
Height	13.2 mm	Height (inches)	0.5197 inch
Width	15.6 mm	Width (inches)	0.6142 inch
Net weight	0.97 g		

Temperatures

Storage temperature		Operating temperature	-40 °C...70 °C
Installation temperature			

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Description of article	Bulkhead insert SCRJ to 2 SC, singlemode	Colour	Miscellaneous
Housing main material	PA	Protection degree	IP67 with housing
Plugging cycles	1000	Composition	Connector and flange insert for variant 1, 4 and 14 housings
Fibre type	Singlemode	Insertion loss	≤ 0.5 dB
Connection 1	SC	Connection 2	SCRJ
Return loss (attenuation)	≥ 40 dB		

General standards

Connector standard	IEC 61754-4, IEC 61754-24

Classifications

ETIM 8.0	EC000752	ETIM 9.0	EC000752
ETIM 10.0	EC000752	ECLASS 14.0	19-17-01-16
ECLASS 15.0	19-17-01-16		

IE-BI-SCRJ2SC-SM-C

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing