

## IE-PS-V01M-RJ45-FH

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Bayonet plug-in connector sets according to IEC  
61076-3-106 ver.1 (EtherNet/IP), RJ45 metal insert incl.  
RJ45 insert

### General ordering data

Version	RJ45 plug, no tools required, Variant 1 metal, Cat.6A / Class EA (ISO/IEC 11801 2010)
Order No.	<a href="#">1963120000</a>
Type	IE-PS-V01M-RJ45-FH
GTIN (EAN)	4032248651627
Qty.	10 items

## IE-PS-V01M-RJ45-FH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

## Dimensions and weights

Net weight 107.01 g

## Temperatures

Storage temperature Operating temperature -40 °C...70 °C

Installation temperature

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1

SCIP e5bbf197-73b5-420b-90c0-0173b7b3b6b7

## General data

Connection 1	RJ45	Connection 2	IDC
Description of article	Variant 1 metal	Colour	black
Housing main material	Zinc diecast	Insulation cross-section, min.	0.85 mm
Insulation cross-section, max.	1.6 mm	Category	Cat.6A / Class EA (ISO/IEC 11801 2010)
Contact surface	Gold over nickel	Connection diameter, solid	0.4...0.64 mm
Conductor connection cross-section, solid (AWG)	AWG 24...AWG 22	Connection diameter, flexible	0.48...0.76 mm
Conductor connection cross-section, flexible (AWG)	AWG 26...AWG 22	MICE classification M	M3
MICE classification I	I3	MICE classification C	C1
MICE classification E	E3	Sheath diameter, min.	5 mm
Sheath diameter, max.	10 mm	Shielding	360°; all-round enclosure
Protection degree	IP67	Plugging cycles	750
Ability to reconnect	≥ 10 cycles (for the same or larger cross-section)		

## Electrical properties

Dielectric strength, contact / shield ≥ 1500 V AC/DC Dielectric strength, contact / contact ≥ 1000 V AC/DC

## General standards


Connector standard	IEC 61076-3-106 Var. 1, IEC 60603-7-51	Application-specific communication cable facilities	PROFINET installation instructions
Certificate no. (cULus)	E316369		

**Technical data**

**Classifications**

ETIM 8.0	EC001121	ETIM 9.0	EC001121
ETIM 10.0	EC001121	ECLASS 14.0	27-44-03-90
ECLASS 15.0	27-44-03-90		

**Dimensioned drawing**



## IE-PS-V01M-RJ45-FH

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

# Accessories

## Dust caps




For protecting your devices against dust and dirt.

### General ordering data

Type	IE-PP-V01P	Version	
Order No.	<a href="#">1965690000</a>	Plug housing protective cap	
GTIN (EAN)	4032248653911		
Qty.	10 ST		

## Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

Type	ESG 9/11 K MC NE WS	Version	
Order No.	<a href="#">1857440000</a>	ESG, Device markers x 11 mm, PA 66, Colour: white, Self-adhesive	
GTIN (EAN)	4032248402731		
Qty.	200 ST		

