

## IE-BS-V01M-SCRJ2SC-SM-C

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Bayonet plug-in connector sets according to IEC  
61076-3-106 ver.1 (EtherNet/IP), RJ45 metal insert incl.  
SC insert

### General ordering data

Version	Flange FO, IP67, Version 1, coupling from SCRJ on 2*SC, Singlemode
Order No.	<a href="#">1963440000</a>
Type	IE-BS-V01M-SCRJ2SC-SM-C
GTIN (EAN)	4032248645534
Qty.	10 items

## IE-BS-V01M-SCRJ2SC-SM-C

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Depth	36.6 mm	Depth (inches)	1.4409 inch
Height	32 mm	Height (inches)	1.2598 inch
Width	32 mm	Width (inches)	1.2598 inch
Net weight	62.1 g		

### Temperatures

Storage temperature	Operating temperature	-40 °C...70 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	c1a8d9e9-fd0c-4258-8c31-7317a7b4ce18

### General data

Description of article	Version 1, coupling from SCRJ on 2*SC	Colour	Miscellaneous
Housing main material	Zinc diecast	Protection degree	IP67
Plugging cycles	500	Fibre type	Singlemode
Insertion loss	≤ 0.5 dB	Connection 1	SC
Connection 2	SCRJ	Return loss (attenuation)	≥ 40 dB

### General standards

Connector standard	IEC 61076-3-106 Var. 1, IEC 61754-4, IEC 61754-24
--------------------	---

### Classifications

ETIM 8.0	EC000752	ETIM 9.0	EC000752
ETIM 10.0	EC000752	ECLASS 14.0	19-17-01-16
ECLASS 15.0	19-17-01-16		

**Installation cut-out**



Mounting cut-out: 1. With central screw connection / 2. For mounting with four M3 screws

**Detailed drawing**



Wall thickness when using the central screw connection