

IE-BH-V05M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



HDC plug-in connector according to IEC 61076-3-106
ver.5 in metal, empty housing

General ordering data

Version	Empty enclosure, Flange-mounted housing, Variant 5 to IEC 61076-3-106, IP67
Order No.	1963530000
Type	IE-BH-V05M
GTIN (EAN)	4032248645626
Qty.	10 items

IE-BH-V05M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

Dimensions and weights

Depth	22.4 mm	Depth (inches)	0.8819 inch
Height	40 mm	Height (inches)	1.5748 inch
Width	28 mm	Width (inches)	1.1024 inch
Net weight	33.6 g		

Temperatures

Storage temperature Operating temperature -40 °C...70 °C

Installation temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	3767b26f-703a-492e-9234-36e83d1c0725

General data

Colour	Miscellaneous	Housing main material	diecast aluminium
Type of mounting	2 screws	Protection degree	IP67
Plugging cycles	750		

General standards

Connector standard	IEC 61076-3-106 Var. 5	Certificate no. (cULus)	E316369
--------------------	------------------------	-------------------------	---------

Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-01-04
ECLASS 15.0	27-19-01-04		

Dimensioned drawing

