

VH 25.2/8/6.4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The additional connection enables a separate voltage tap. This can be used, for example, for the emergency power supply before the main switch or simply as an additional connection within the application.

General ordering data

Version	W-Series, Spacer sleeve
Order No.	1967110000
Type	VH 25.2/8/6.4
GTIN (EAN)	4032248739196
Qty.	5 items
Delivery status	This article will no longer be available in the future.
Last order date	2027-04-30T00:00:00+02:00

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	25.2 mm	Depth (inches)	0.9921 inch
Diameter	8 mm	Net weight	3.95 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	tinned copper	Colour	Silver grey
----------------	---------------	--------	-------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Dimensions

Diameter	8 mm
----------	------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 8.0	EC002848	ETIM 9.0	EC002848
ETIM 10.0	EC002848	ECLASS 14.0	27-25-03-90
ECLASS 15.0	27-25-03-90		

