

DGSB IP30 D0 PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Intelligent cabling solutions can save you valuable time and money.

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

General ordering data

Version	Field Power® sealing insert, Blank seal, IP30, with corresponding enclosure, TPE-U
Order No.	1967600000
Type	DGSB IP30 D0 PT6
GTIN (EAN)	4032248688746
Qty.	10 items
Delivery status	Discontinued

DGSB IP30 D0 PT6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	3.15 mm	Depth (inches)	0.124 inch
Height	23.51 mm	Height (inches)	0.9256 inch
Width	35 mm	Width (inches)	1.378 inch
Net weight	1.6 g		

Temperatures

Storage temperature	-40 °C...55 °C	Operating temperature	-40 °C...55 °C
---------------------	----------------	-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Basic material	TPE-U	Silicone	No
Colour	grey	Design	Blank seal
Protection degree	IP30, with corresponding enclosure	Mounting position, installation notice	in FieldPower® IP30 sealing slot

Classifications

ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		