

HDC 24B KLU 1M25G
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Version	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Coupling housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25
Order No.	1968340000
Type	HDC 24B KLU 1M25G
GTIN (EAN)	4032248689378
Qty.	1 items

HDC 24B KLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

Dimensions and weights

Height	63.8 mm	Height (inches)	2.5118 inch
Width	73.8 mm	Width (inches)	2.9055 inch
Net weight	342 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-0dda3647412f

Chemical resistance	Substance	Acetone
	Chemical resistance	Conditionally resistant
	Substance	Drilling oil
	Chemical resistance	Resistant
	Substance	Diesel
	Chemical resistance	Resistant
	Substance	Ethyl alcohol
	Chemical resistance	Resistant
	Substance	Transmission oil
	Chemical resistance	Resistant
	Substance	Hydraulic oil
	Chemical resistance	Resistant
	Substance	Coolant
	Chemical resistance	Resistant
	Substance	Petroleum benzine
	Chemical resistance	Resistant
	Substance	Sweat
	Chemical resistance	Resistant
	Substance	Premium gasoline
	Chemical resistance	Conditionally resistant
Substance	Water	
Chemical resistance	Resistant	
Substance	UV	
Chemical resistance	Unstable	
Substance	Ozone	
Chemical resistance	Unstable	

Dimensions

Cable entry	w. thread	Width housing C	43 mm
Total length housing	120 mm	Height of housing B	66 mm

HDC 24B KLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General data

Housing main material	diecast aluminium	Surface finish	Powder coating
Protection degree	IP65, in plugged condition	EMC housings	No
Material of locking element	Stainless steel, rust-proof		

Version

Size of cable entries	M 25	Top part/bottom part/lid	lower part
Cover	without cover	Number of cable entry on top	1
Number of cable entry sideways	0	Design of housing	Coupling housing
Design of locking system	End-locking clamp, lower side	Design	Standard
Installation size	8	Cable entry	w. thread
Type	coupling extension	Clamp version	End-locking clamp
Sealing	NBR	Internal thread	M 25
Colour (RAL)	RAL 7035	BG	8
Suitable for ModuPlug®	No		

Classifications


ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

HDC 24B KLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC 24B KLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

XXL plug housing, cable entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 64D TSLU 1M50G	Version	
Order No.	1111150000		HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4032248100118		plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST		clamp, lower side, Standard, Size of cable entries: M 50

Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings. The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact. The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening. The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned. Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 24B TSLU 1PG21G	Version	
Order No.	1662390000		HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4008190418915		plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST		clamp, lower side, Standard, Size of cable entries: PG 21
Type	HDC 24B TSLU 1PG29G	Version	
Order No.	1662410000		HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4008190418939		plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST		clamp, lower side, Standard, Size of cable entries: PG 29

HDC 24B KLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	HDC 64D TSLU 1PG21G	Version
Order No.	1662470000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4008190418991	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: PG 21
Type	HDC 64D TSLU 1PG29G	Version
Order No.	1662490000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4008190419011	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: PG 29
Type	HDC 64D TSLU 1M32G	Version
Order No.	1786810000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4032248204052	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: M 32
Type	HDC 24B TSLU 1M32G	Version
Order No.	1787790000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4032248205233	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: M 32
Type	HDC 24B TSLU 1M25G	Version
Order No.	1787800000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4032248205240	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: M 25
Type	HDC 64D TSLU 1M40G	Version
Order No.	1804610000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4032248267538	plugged condition, Cable entry from side, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: M 40

XXL plug housing, cable entry on top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 64D TOLU 1M50G	Version
Order No.	1111170000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4032248100125	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, Standard, Size of cable entries: M 50

HDC 24B KLU 1M25G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 24B TOLU 1PG21G	Version
Order No.	1662540000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 21
GTIN (EAN)	4008190419066	
Qty.	1 ST	
Type	HDC 24B TOLU 1PG29G	Version
Order No.	1662550000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: PG 29
GTIN (EAN)	4008190419073	
Qty.	1 ST	
Type	HDC 64D TOLU 1PG21G	Version
Order No.	1662610000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: PG 21
GTIN (EAN)	4008190419134	
Qty.	1 ST	
Type	HDC 64D TOLU 1PG29G	Version
Order No.	1662630000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: PG 29
GTIN (EAN)	4008190419158	
Qty.	1 ST	
Type	HDC 64D TOLU 1M32G	Version
Order No.	1786860000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: M 32
GTIN (EAN)	4032248204106	
Qty.	1 ST	
Type	HDC 64D TOLU 1M25G	Version
Order No.	1786870000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, high, Size of cable entries: M 25
GTIN (EAN)	4032248204113	
Qty.	1 ST	
Type	HDC 24B TOLU 1M32G	Version
Order No.	1787850000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: M 32
GTIN (EAN)	4032248205295	
Qty.	1 ST	
Type	HDC 24B TOLU 1M25G	Version
Order No.	1787860000	HDC enclosures, Installation size: 8, Protection degree: IP65, in plugged condition, Cable entry from top, Plug housing, End-locking clamp, lower side, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248205301	
Qty.	1 ST	

HDC 24B KLU 1M25G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	HDC 64D TOLU 1M40G	Version
Order No.	1983470000	HDC enclosures, Installation size: 8, Protection degree: IP65, in
GTIN (EAN)	4032248687916	plugged condition, Cable entry from top, Plug housing, End-locking
Qty.	1 ST	clamp, lower side, high, Size of cable entries: M 40