


## HDC CFM 6 2F

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The sturdy CR6 module frames are available in polycarbonate or die-cast zinc. The frames are designed so that two individual modules or a double module can be installed. The CR6 frames are designed to fit the size-3 housings.

### General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept frame
Order No.	<a href="#">1983840000</a>
Type	HDC CFM 6 2F
GTIN (EAN)	4032248688975
Qty.	1 items

## HDC CFM 6 2F

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

## Dimensions and weights

Depth	51 mm	Depth (inches)	2.0079 inch
Height	35 mm	Height (inches)	1.378 inch
Width	34 mm	Width (inches)	1.3386 inch
Net weight	70.66 g		

## Temperatures

Limit temperature -40 °C ... 125 °C

## Environmental Product Compliance

RoHS Compliance Status Compliant

REACH SVHC Lead 7439-92-1

SCIP fa505316-3e43-4ad0-930c-360dfdbe182a

## ConCept Pneumatic module

Colour Silver grey

## Dimensions

Width	34 mm	Total length base	51 mm
Height of socket	35 mm		

## General data

Tightening torque	0.5 Nm	Installation size	3
Colour	Silver grey	Tightening torque, max. PE connection	1.5 Nm
Type	Female	Tightening torque, min. PE connection	0.5 Nm
Basic material	Diecast zinc	Series	ConCept frame
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes
BG	3		

## Connection data PE

Connection type PE	Screw connection	Tightening torque, max. PE connection	1.5 Nm
Tightening torque, min. PE connection	0.5 Nm		

## Version

Installation size	3	Basic material	Diecast zinc
BG	3		

**Technical data**

**Classifications**

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		