

## HDC CFM 10 3F

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



The sturdy CR10 module frames are available in polycarbonate or die-cast zinc.

The frames are designed so that 3 individual modules or corresponding double modules can be installed. The CR10 frames are designed to fit the size-4 housings.

### General ordering data

Version	Heavy-duty connectors, HDC insert, ConCept frame
Order No.	<a href="#">1983860000</a>
Type	HDC CFM 10 3F
GTIN (EAN)	4032248688999
Qty.	1 items

## HDC CFM 10 3F

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E92202

### Dimensions and weights

Depth	64 mm	Depth (inches)	2.5197 inch
Height	35 mm	Height (inches)	1.378 inch
Width	34 mm	Width (inches)	1.3386 inch
Net weight	76.88 g		

### Temperatures

Limit temperature -40 °C ... 125 °C

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

### ConCept Pneumatic module

Colour Silver grey

### Dimensions

Width	34 mm	Total length base	64 mm
Height of socket	35 mm		

### General data

Tightening torque	0.5 Nm	Installation size	4
Colour	Silver grey	Tightening torque, max. PE connection	1.5 Nm
Type	Female	Tightening torque, min. PE connection	0.5 Nm
Basic material	Diecast zinc	Series	ConCept frame
Free from halogens	false	Low smoke acc. DIN EN 45545-2	Yes
BG	4		

### Connection data PE

Connection type PE	Screw connection	Tightening torque, max. PE connection	1.5 Nm
Tightening torque, min. PE connection	0.5 Nm		

### Version

Installation size	4	Basic material	Diecast zinc
BG	4		

**Technical data**

**Classifications**

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		

## HDC CFM 10 3F

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Modul removal tool




Weidmüller offers a variety of crimping tools, no-contact tools, and fibre optic tools.

#### General ordering data

Type	HDC-DW-MOD	Version	
Order No.	<a href="#">1688200000</a>	Tool miscellaneous, Contact Removal Tool	
GTIN (EAN)	4008190857189		
Qty.	1 ST		

### Slotted screwdriver



VDE insulated slot-head screwdriver, SDI DIN 7437, ISO 2380/2, drive output acc. to DIN 5264, ISO 2380/1. SoftFinish grip

#### General ordering data

Type	SDIS 0.6X3.5X100	Version	
Order No.	<a href="#">9008390000</a>	Screwdriver, Screwdriver	
GTIN (EAN)	4032248056354		
Qty.	1 ST		
Type	SDS 0.6X3.5X100	Version	
Order No.	<a href="#">9008330000</a>	Screwdriver, Screwdriver	
GTIN (EAN)	4032248056286		
Qty.	1 ST		