

**FAD BLK7 2XHE20 M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The FAD TSX front adapters with pre-assembled cables provide safe migration from the TSX cards to other PLC systems or to the u-remote modules from Weidmüller.

- Can be plugged into TS35 terminal rail

**General ordering data**

Order No.	1985960000
Type	<a href="#">FAD BLK7 2XHE20 M</a>
GTIN (EAN)	4050118371000
Qty.	1 items

## FAD BLK7 2XHE20 M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	36 mm	Depth (inches)	1.4173 inch
Height	218 mm	Height (inches)	8.5827 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	210 g		

### Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50
---------------------	-------------	-----------------------	----------

### Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

### Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---

### Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---

### Ratings data

Operating voltage	30 V AC / 60 V DC	Max. current per channel	1 A
Max. current per byte	2 A	Total operating current	6 A

### Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 250 V AC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage AC	1.2 kV	Storage temperature, min.	-40 °C
Storage temperature, max.	60 °C		

### Classifications

ETIM 8.0	EC002780	ETIM 9.0	EC002780
ETIM 10.0	EC002780	ECLASS 14.0	27-14-11-52
ECLASS 15.0	27-14-11-52		

**FAD BLK7 2XHE20 M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

