

FAD S5115 SL24 M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The FAD S5-115 front adapters with pre-assembled cables provide safe migration from the old S5-115 to other PLC systems or to the u-remote system from Weidmüller.

- Clip-in foot for TS35
- S5-115 card is powered by a single power supply

General ordering data

Order No.	1985980000
Type	FAD S5115 SL24 M
GTIN (EAN)	4050118371109
Qty.	1 items

FAD S5115 SL24 M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	25 mm	Depth (inches)	0.9842 inch
Height	280 mm	Height (inches)	11.0236 inch
Width	46 mm	Width (inches)	1.811 inch
Net weight	176 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	9d5ff7ee-74dc-449b-a1db-a29604b9b3e9

Connection data

Connection (field side)	SL 5.08 mm
-------------------------	------------

Connection data

Connection (field side)	SL 5.08 mm
-------------------------	------------

Ratings data

Operating voltage	250 V AC	Max. current per channel	6 A
Total operating current	32 A		

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 250 V AC
Surge voltage category	II	Pollution severity level	2
Insulation test voltage AC	1.2 kV		

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

FAD S5115 SL24 M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

