

FAD S5135 2XHE20 32IO R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The FAD S5-135 front adapters with pre-assembled cables provide safe migration from the old S5-135 to other PLC systems or to the u-remote system from Weidmüller.

- S5-135 card is powered by a single power supply

General ordering data

Order No.	1986050000
Type	FAD S5135 2XHE20 32IO R
GTIN (EAN)	4050118370959
Qty.	1 items

FAD S5135 2XHE20 32IO R

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	36 mm	Depth (inches)	1.4173 inch
Height	283 mm	Height (inches)	11.1417 inch
Width	20 mm	Width (inches)	0.7874 inch
Net weight	65 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	9d5ff7ee-74dc-449b-a1db-a29604b9b3e9

Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---

Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---

Ratings data

Operating voltage	30 V AC / 60 V DC	Max. current per channel	1 A
Max. current per byte	2 A	Total operating current	6 A

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 50 V AC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage AC	0.35 kV		

Classifications

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

FAD S5135 2XHE20 32IO R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

