



- For conductors from 10.0 to 185.0 mm² (AWG 7 - 350 MCM)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
- supplied loose in poly-bag

General ordering data

Version	Wire-end ferrule, Standard, 25 mm, 25 mm, No
Order No.	1988780000
Type	H50,0/25
GTIN (EAN)	4050118373509
Qty.	100 items
Packaging	loose

H50,0/25

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	2.05 g
------------	--------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard
------------------------	---	---------	----------

Wire-end ferrules

Contact surface diameter (D1)	10.3 mm	Contact surface length (L2)	25 mm
Collar diameter (D2)	13 mm	L1 in mm	25.00 mm
Wire connection cross section AWG, max.	AWG 1	Stripping length	25 mm
Conductor cross-section	50 mm ²		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

