

IE-FC-SET-SPDEK001-KY-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Set
Order No.	1989020000
Type	IE-FC-SET-SPDEK001-KY-P
GTIN (EAN)	4050118373615
Qty.	1 items

IE-FC-SET-SPDEK001-KY-P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Depth	134 mm	Depth (inches)	5.2756 inch
Height	40 mm	Height (inches)	1.5748 inch
Width	67 mm	Width (inches)	2.6378 inch
Net weight	494 g		

Temperatures

Storage temperature
Installation temperature

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	8a473a8a-33d4-4318-8088-c28f019e7f77

General data

Product type	Set	
Protection degree	IP65, in closed state	
Material frame	Zinc diecast	
Material cover	Polycarbonate PC	
Reference product	IE-FC-SFP-KEY2 , IE-FC-SP-PWB/2ST , IE-FCI-PWB-DE , IE-BI-USB-A , IE-BI-RJ45-C , IE-FC-PWPC	
Reference product	Cardinality	1
	Reference	IE-FC-SFP-KEY2
	Cardinality	1
	Reference	IE-FC-SP-PWB/2ST
	Cardinality	1
	Reference	IE-FCI-PWB-DE
	Cardinality	1
	Reference	IE-BI-USB-A
	Cardinality	1
	Reference	IE-BI-RJ45-C
	Cardinality	1
	Reference	IE-FC-PWPC

Technical data

Printing	Incl. fixed inscription: "Service only!", "USB", "Ethernet", "230 V AC"	Insert plate	2x data, 1x power, Shielded
Frame	Plastic cover, Lockable with key	Rated voltage for socket	250 V
Power inserts	Socket DE	Data inserts	USB 2.0 A/A, RJ45 coupling Cat.6A
Rated current for socket	16 A		

IE-FC-SET-SPDEK001-KY-P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****General standards**

Certificate No. (DNV)	TAA000022B
-----------------------	------------

Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

IE-FC-SET-SPDEK001-KY-P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

