


**THM ET S7 1500 TU****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

**General ordering data**

Version	THM, Device markers, 108.8 x 22.9 mm, Siemens, Turquoise
Order No.	<a href="#">1991680000</a>
Type	THM ET S7 1500 TU
GTIN (EAN)	4050118376333
Qty.	500 items

## THM ET S7 1500 TU

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	108.8 mm	Height (inches)	4.2835 inch
Width	22.9 mm	Width (inches)	0.9016 inch
Net weight	0.68 g		

## Temperatures

Operating temperature range	-50...100 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## General data

Printing method	Thermal transfer	
Version	halogen-free	
Width	22.9 mm	
UL 94 flammability rating	HB	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-50 °C	
Colour	Turquoise	
Halogen	No	
Basic material	Polypropylene	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Approval acc. to UL 969	No	
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>	
Number of markers per combination	1 Label reel = Device markers	
Operating temperature range	-50...100 °C	
Application/manufacturer	Siemens	
Number per roll	500	

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		