

## IE-USB-A-A-0.5M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Assembled IE cables

### General ordering data

Version	USB cable, USB A, USB A, PVC, 0.5 m
Order No.	<a href="#">1993550005</a>
Type	IE-USB-A-A-0.5M
GTIN (EAN)	4050118378542
Qty.	1 items

**IE-USB-A-A-0.5M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Length	0.5 m	Length (inches)	19.685 inch
Net weight	26 g		

**Temperatures**

Storage temperature	Operating temperature	-15 °C...80
Installation temperature		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Technical specifications for cable**

Sheathing colour black

**General technical data**

Contact surface Gold over nickel

**Cable structure**

Sheath diameter	4.5 mm	Sheathing colour	black
Cross-section	2*AWG28 + 2*AWG24	Sheath diameter, max.	4.7 mm
Sheath diameter, min.	4.3 mm	Material sheath	PVC

**Plug, left**

Plug left USB A, IP20, male contact, straight, plug, Plastic, shielded

**Plug, right**

Plug right USB A, IP20, male contact, straight, plug, Plastic, shielded

**Classifications**

ETIM 8.0	EC001408	ETIM 9.0	EC001408
ETIM 10.0	EC001408	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		