

IE-USB-A-A-3.0M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Assembled IE cables

General ordering data

Version	USB cable, USB A, USB A, PVC, 3 m
Order No.	1993550030
Type	IE-USB-A-A-3.0M
GTIN (EAN)	4050118378566
Qty.	1 items

IE-USB-A-A-3.0M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Length	3 m	Length (inches)	118.1102 inch
Net weight	58 g		

Temperatures

Storage temperature	Operating temperature	-15 °C...80
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical specifications for cable

Sheathing colour	black
------------------	-------

General technical data

Contact surface	Gold over nickel
-----------------	------------------

Cable structure

Sheath diameter	4.5 mm	Sheathing colour	black
Cross-section	2*AWG28 + 2*AWG24	Sheath diameter, max.	4.7 mm
Sheath diameter, min.	4.3 mm	Material sheath	PVC

Plug, left

Plug left	USB A, IP20, male contact, straight, plug, Plastic, shielded
-----------	--

Plug, right

Plug right	USB A, IP20, male contact, straight, plug, Plastic, shielded
------------	--

Classifications

ETIM 8.0	EC001408	ETIM 9.0	EC001408
ETIM 10.0	EC001408	ECLASS 14.0	27-06-01-06
ECLASS 15.0	27-06-01-06		