

**HDC XX5E01 MOXXXXX-0050**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

Order No.	2003890050
Type	<a href="#">HDC XX5E01 MOXXXXX-0050</a>
GTIN (EAN)	4050118521528
Qty.	1 items

## HDC XX5E01 MOXXXXX-0050

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Net weight	0 g
------------	-----

## Temperatures

Limit temperature	-30 °C ... 90 °C
-------------------	------------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5

## General data

Number of poles	4	Cable length	0.5 m
Coding	D-coded	Contact surface	Au (Gold)
Transmission rate	100 MBit/s	Insulation resistance	≥ 108 Ω
Category	Cat. 5e	Nominal voltage	250 V
Nominal current	4 A	Plugging cycles	≥ 100
Type	Pin	Pollution severity	2
Opposite side version	open	Module side version	Male

## Cable technical specifications

Cable length	0.5 m	
Sheathing colour	green	
Shielded	Yes	
Halogen	No, halogen-free	
Insulation	PE	
Sheath material	PUR	
Colour coding	white, yellow, blue, orange	
Outside diameter	Diameter	6.5 mm
	Signs	±
	Tolerance	0.2
Outside diameter	6.5 mm ± 0.2	

## Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-07
ECLASS 15.0	27-06-03-07		

**HDC XX5E01 MOXXXXX-0050**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

---

---

	M12
yellow	1
white	2
orange	3
blue	4

---

---