

HDC XX5E01 MOXXXXX-1500

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

| | |
|------------|-----------------------------------------|
| Order No. | 2003891500 |
| Type | HDC XX5E01 MOXXXXX-1500 |
| GTIN (EAN) | 4050118521610 |
| Qty. | 1 items |

HDC XX5E01 MOXXXXX-1500

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | |
|------------|-----|
| Net weight | 0 g |
|------------|-----|

Temperatures

| | |
|-------------------|------------------|
| Limit temperature | -30 °C ... 90 °C |
|-------------------|------------------|

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5 |

General data

| | | | |
|-----------------------|------------|-----------------------|-----------|
| Number of poles | 4 | Cable length | 15 m |
| Coding | D-coded | Contact surface | Au (Gold) |
| Transmission rate | 100 MBit/s | Insulation resistance | ≥ 108 Ω |
| Category | Cat. 5e | Nominal voltage | 250 V |
| Nominal current | 4 A | Plugging cycles | ≥ 100 |
| Type | Pin | Pollution severity | 2 |
| Opposite side version | open | Module side version | Male |

Cable technical specifications

| | | |
|------------------|-----------------------------|--------|
| Cable length | 15 m | |
| Sheathing colour | green | |
| Shielded | Yes | |
| Halogen | No, halogen-free | |
| Insulation | PE | |
| Sheath material | PUR | |
| Colour coding | white, yellow, blue, orange | |
| Outside diameter | Diameter | 6.5 mm |
| | Signs | ± |
| | Tolerance | 0.2 |
| Outside diameter | 6.5 mm ± 0.2 | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-07 |
| ECLASS 15.0 | 27-06-03-07 | | |

HDC XX5E01 MOXXXXX-1500

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

| | M12 |
|--------|-----|
| yellow | 1 |
| white | 2 |
| orange | 3 |
| blue | 4 |
