


HDC XX5E02 FOXXXXX-0050

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Order No.	2003930050
Type	HDC XX5E02 FOXXXXX-0050
GTIN (EAN)	4050118521191
Qty.	1 items

HDC XX5E02 FOXXXXX-0050

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Net weight	47.52 g
------------	---------

Temperatures

Limit temperature	-40 °C ... 90 °C
-------------------	------------------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5

General data

Number of poles	4	Cable length	0.5 m
Coding	D-coded	Contact surface	Au (Gold)
Transmission rate	100 MBit/s	Insulation resistance	≥ 108 Ω
Category	Cat. 5e	Nominal voltage	250 V
Nominal current	4 A	Plugging cycles	≥ 2265 100
Type	Female	Pollution severity	2
Opposite side version	open	Module side version	Female

Cable technical specifications

Cable length	0.5 m	
Sheathing colour	blue	
Shielded	Yes	
Halogen	Yes, No	
Sheath material	Radox EM 104	
Colour coding	white, yellow, blue, orange	
Outside diameter	Diameter	7.25 mm
	Signs	±
	Tolerance	0.3
Outside diameter	7.25 mm ± 0.3	

Classifications

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-07
ECLASS 15.0	27-06-03-07		