

ELS 8/20 MM WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



ELS

ELS tags are special and non-adhesive insertable labels for WKM cable markers or for group tag carriers. The matt, thin but tear-resistant polyester provides very good labelling and excellent readability. Used in combination with water-repellent WKM sleeves, the solution guarantees particularly long-lasting identification of cables even in harsh environments.

General ordering data

Version	ELS, Insert markers, 7 - 115 mm, 20 x 8 mm, white
Order No.	2005 180000
Type	ELS 8/20 MM WS
GTIN (EAN)	4050118389968
Qty.	3000 items

ELS 8/20 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.14 mm	Depth (inches)	0.0055 inch
Height	20 mm	Height (inches)	0.7874 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	0.04 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Type of printing	neutral	Version	halogen-free
Width	8 mm	UL 94 flammability rating	HB
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Colour	white	Halogen	No
Basic material	Polyester	Printed characters	without
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	Operating temperature range	-40...150 °C
Number per roll	3000		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	150 mm ²
Conductor O.D., max.	115 mm	Conductor O.D., min.	7 mm
Conductor O.D.	7 - 115 mm	Cross-section for connected wire	150 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

Drawings

