

TM-I 15 MM WS


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Process reliability: TM-I

TM-I inlay tags have a guide tab which allows them to slide easily into the transparent sleeves from the type TM. Once the tag is in place, the tab is snapped off at the pre-determined break point. The ready-assembled sleeves can then be simply pushed over the conductors. Your benefits: large quantities can be efficiently pre-assembled in a single step.

General ordering data

Version	TM-I, Insert markers, 1.3 - 35 mm, 15 x 4 mm, white
Order No.	2005450000
Type	TM-I 15 MM WS
GTIN (EAN)	4050118390346
Qty.	2000 items

TM-I 15 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	15 mm	Height (inches)	0.5906 inch
Width	4 mm	Width (inches)	0.1575 inch
Net weight	0.16 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Orientation of print	horizontal and vertical	Type of printing	neutral
Width	4 mm	UL 94 flammability rating	HB
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Colour	white	Halogen	No
Basic material	Polyester	Printed characters	without
compatible printer	THM MULTIMARK , THM MULTIMARK PLUS	Operating temperature range	-40...150 °C
Number per roll	2000		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	70 mm ²
Conductor O.D., max.	35 mm	Conductor O.D., min.	1.3 mm
Conductor O.D.	1.3 - 35 mm	Cross-section for connected wire	70 mm ²

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

