

## WS 10/5 M PLUS MC SDR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



WS markers are the perfect match for the W-series connectors. Thanks to their system compatibility, the WS tags can also be used with the I-series and the Z-series. The large marking surfaces do not only permit long character strings but also multi-line text.

WS markers are ideal for labels with long, customised character strings. Thanks to the proven MultiCard format, printing with PrintJet CONNECT oder/or Plotter is possible.

- Can be fitted in strips or individually
- Markers in proven MultiCard format

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

### General ordering data

|            |   |
|------------|---|
| Version    | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, Allen-Bradley, To customer specification |
| Order No.  | <a href="#">2007770000</a>  |
| Type       | WS 10/5 M PLUS MC SDR   |
| GTIN (EAN) | 4050118393279   |
| Qty.       | 120 items   |

**WS 10/5 M PLUS MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Height     | 10 mm  | Height (inches) | 0.3937 inch |
| Width      | 5 mm   | Width (inches)  | 0.1968 inch |
| Net weight | 0.12 g |                 |             |

**Temperatures**

Operating temperature range -40...100 °C

**Environmental Product Compliance**

|                          |                             |                 |  |
|--------------------------|-----------------------------|-----------------|--|
| RoHS Compliance Status   | Compliant without exemption |                 |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                 |  |
| Product Carbon Footprint | Cradle to gate              | 0.001 kg CO2eq. |  |

**General data**

|                                      |                               |           |  |
|--------------------------------------|-------------------------------|-----------|--|
| Printing method                      | MC Laser                      |           |  |
| Width                                | 5 mm                          |           |  |
| UL 94 flammability rating            | V-2                           |           |  |
| Operating temperature range, max.    | 100 °C                        |           |  |
| Operating temperature range, min.    | -40 °C                        |           |  |
| Colour                               | To customer specification     |           |  |
| Halogen                              | No                            |           |  |
| Basic material                       | Polyamide 66                  |           |  |
| Colour of printing                   | black                         |           |  |
| Printed characters                   | Requires M-Print PRO File     |           |  |
| Number of markers per packaging unit | Form of supply                | MultiCard |  |
| Number of markers per combination    | 1 MultiCard = Terminal marker |           |  |
| Operating temperature range          | -40...100 °C                  |           |  |
| Application/manufacturer             | Weidmueller, Allen-Bradley    |           |  |

**Connector markers**

Pitch in mm (P) 5.00 mm

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000761    | ETIM 9.0    | EC000761    |
| ETIM 10.0   | EC000761    | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 |             |             |

**WS 10/5 M PLUS MC SDR**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

**Similar to illustration**

---



**Drawing**

---

