

HDC 24D KBU 1PG29G CS**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | |
|------------|--|
| Version | HDC enclosures, Installation size: 4, Protection degree: IP65, in plugged condition, Coupling housing, Side-locking clamp on lower side, , Size of cable entries: 1*PG29 |
| Order No. | 2007940000 |
| Type | HDC 24D KBU 1PG29G CS |
| GTIN (EAN) | 4050118393965 |
| Qty. | 1 items |

HDC 24D KBU 1PG29G CS

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 43 mm | Depth (inches) | 1.6929 inch |
| Height | 75 mm | Height (inches) | 2.9527 inch |
| Width | 116 mm | Width (inches) | 4.5669 inch |
| Length | 116 mm | Length (inches) | 4.5669 inch |
| Net weight | 218.24 g | | |

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

| | | |
|------------------------|--|-------------------------|
| RoHS Compliance Status | Compliant without exemption | |
| REACH SVHC | Potassium perfluorobutane sulfonate 29420-49-3 | |
| SCIP | e98b2b24-ba23-41bf-8d19-0dda3647412f | |
| Chemical resistance | Substance | Acetone |
| | Chemical resistance | Conditionally resistant |
| | Substance | Drilling oil |
| | Chemical resistance | Resistant |
| | Substance | Diesel |
| | Chemical resistance | Resistant |
| | Substance | Ethyl alcohol |
| | Chemical resistance | Resistant |
| | Substance | Transmission oil |
| | Chemical resistance | Resistant |
| | Substance | Hydraulic oil |
| | Chemical resistance | Resistant |
| | Substance | Coolant |
| | Chemical resistance | Resistant |
| | Substance | Petroleum benzine |
| | Chemical resistance | Resistant |
| | Substance | Sweat |
| | Chemical resistance | Resistant |
| | Substance | Premium gasoline |
| | Chemical resistance | Conditionally resistant |
| | Substance | Water |
| | Chemical resistance | Resistant |
| | Substance | UV |
| | Chemical resistance | Unstable |
| | Substance | Ozone |
| | Chemical resistance | Unstable |

Dimensions

| | | | |
|---------------------|-----------|-----------------|-------|
| Cable entry | w. thread | Width housing C | 43 mm |
| Height of housing B | 54.65 mm | | |

HDC 24D KBU 1PG29G CS

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**General data**

| | | | |
|-----------------------------|-----------------------------|-------------------|----------------------------|
| Surface finish | Powder coating | Protection degree | IP65, in plugged condition |
| Material of locking element | Stainless steel, rust-proof | | |

Version

| | | | |
|--------------------------------|----------------------------------|------------------------------|--------------------|
| Size of cable entries | 1*PG29 | Top part/bottom part/lid | lower part |
| Cover | without cover | Number of cable entry on top | 1 |
| Number of cable entry sideways | 0 | Design of housing | Coupling housing |
| Design of locking system | Side-locking clamp on lower side | Installation size | 4 |
| Cable entry | w. thread | Clamp version | Side-locking clamp |
| Sealing | NBR | BG | 4 |
| Suitable for ModuPlug® | Yes | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000437 | ETIM 9.0 | EC000437 |
| ETIM 10.0 | EC000437 | ECLASS 14.0 | 27-44-02-02 |
| ECLASS 15.0 | 27-44-02-02 | | |

HDC 24D KBU 1PG29G CS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**Cover**

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | HDC 10B DODQ 4BO | Version |
| Order No. | 1665230000 | HDC enclosures, Installation size: 4, Protection degree: IP65, in |
| GTIN (EAN) | 4008190421939 | plugged condition, Cover for lower part of housing, Side-locking |
| Qty. | 1 ST | clamp on lower side, Standard, Size of cable entries: none |