

## TST 10 SAKC10



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

### General ordering data

Version	Mounting foot for mounting rail, red, Polyamide 66, without, Width: 7.4 mm
Order No.	<a href="#">2082460000</a>
Type	TST 10 SAKC10
GTIN (EAN)	4008190223380
Qty.	400 items

**TST 10 SAKC10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	7.4 mm	Depth (inches)	0.2913 inch
Height	51 mm	Height (inches)	2.0079 inch
Width	7.4 mm	Width (inches)	0.2913 inch
Net weight	3.58 g		

**Temperatures**

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	45173c19-8a33-4947-bc2b-512a20c76dcd		

**Material data**

Basic material	Polyamide 66	Colour	red
UL 94 flammability rating	V-2		

**System specifications**

Version For the mounting rails

**Dimensions**

Internal thread without

**General**

Operating temperature range, max. 100 °C

**Classifications**

ETIM 8.0	EC002625	ETIM 9.0	EC002625
ETIM 10.0	EC002625	ECLASS 14.0	27-18-28-07
ECLASS 15.0	27-18-28-07		