

**TST 10 SAKC10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

**General ordering data**

Version	Mounting foot for mounting rail, red, Polyamide 66, without, Width: 7.4 mm
Order No.	<a href="#">2082460000</a>
Type	TST 10 SAKC10
GTIN (EAN)	4008190223380
Qty.	400 items

**TST 10 SAKC10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Depth	7.4 mm	Depth (inches)	0.2913 inch
Height	51 mm	Height (inches)	2.0079 inch
Width	7.4 mm	Width (inches)	0.2913 inch
Net weight	3.58 g		

**Temperatures**

Ambient temperature	-5 °C...40 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	45173c19-8a33-4947-bc2b-512a20c76dcd		

**Material data**

Basic material	Polyamide 66	Colour	red
UL 94 flammability rating	V-2		

**System specifications**

Version For the mounting rails

**Dimensions**

Internal thread without

**General**

Operating temperature range, max. 100 °C

**Classifications**

ETIM 8.0	EC002625	ETIM 9.0	EC002625
ETIM 10.0	EC002625	ECLASS 14.0	27-18-28-07
ECLASS 15.0	27-18-28-07		