

**SAKQB 6/10****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, grey, Number of poles: 10, Pitch in mm (P): 8.00, Insulated: No, Width: 6 mm
Order No.	<a href="#">2111230000</a>
Type	SAKQB 6/10
GTIN (EAN)	4050118440607
Qty.	10 items
Local product	Only available in certain countries

**Technical data**

**Approvals**

ROHS Conform

**General ordering data**

Local product Only available in certain countries

**Dimensions and weights**

Depth	15 mm	Depth (inches)	0.5906 inch
Width	6 mm	Width (inches)	0.2362 inch
Net weight	19.74 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
---------------------	----------------	---------------------	---------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Material data**

Colour grey

**Additional technical data**

Type of fixing	when screwed in	Explosion-tested version	No
----------------	-----------------	--------------------------	----

**Dimensions**

Pitch in mm (P) 8.00 mm

**General**

Number of poles 10

**Rating data**

Rated voltage 400 V

**Classifications**

ETIM 8.0	EC000489	ETIM 9.0	EC000489
ETIM 10.0	EC000489	ECLASS 14.0	27-25-03-03
ECLASS 15.0	27-25-03-03		