


**PAC-HE10-F-HF-0M5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

Order No.	2420540005
Type	<a href="#">PAC-HE10-F-HF-0M5</a>
GTIN (EAN)	4032248340668
Qty.	1 items

## PAC-HE10-F-HF-0M5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Net weight	24 g
------------	------

### Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50
---------------------	-------------	-----------------------	----------

### Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

### General Data

Cable length	0.5 m	Suitable for	Digital signals
Cable	Cable LIHH	Interface connector	FLAT CABLE CONECTOR HE10 10P
Number of poles, min.	10-pole	Connector PLC side	H0.14/10 (FERRULES 0.14mm <sup>2</sup> )
Wire cross-section	0.14 mm <sup>2</sup>		

### Electrical Data

Total current, max.	3 A	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 V DC ≤ 25 V AC	Resistance	≤ 150 mΩ/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Capacity wire / wires	300 pF/m
Capacity wire / shield	300 pF/m		

### Classifications

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		