

PAC-HE10-HE10-HF-1M5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

| | |
|------------|--------------------------------------|
| Order No. | 2420550015 |
| Type | PAC-HE10-HE10-HF-1M5 |
| GTIN (EAN) | 4099986597143 |
| Qty. | 1 items |

PAC-HE10-HE10-HF-1M5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS Conform

Dimensions and weights

Net weight 72 g

Temperatures

Storage temperature -10...60 °C Operating temperature -10...50 °C

Environmental Product Compliance

RoHS Compliance Status Compliant
 REACH SVHC No SVHC above 0.1 wt%

General Data

| | | | |
|-----------------------|----------------------|---------------------|------------------------------|
| Cable length | 1.5 m | Suitable for | Digital signals |
| Cable | Cable LIHH | Interface connector | FLAT CABLE CONECTOR HE10 10P |
| Number of poles, min. | 10-pole | Connector PLC side | FLAT CABLE CONECTOR HE10 10P |
| Wire cross-section | 0.14 mm ² | | |

Electrical Data

| | | | |
|------------------------|---------------------|---|------------|
| Total current, max. | 3 A | Permissible current strength per path, max. | 1 A |
| Rated voltage | ≤ 60 V DC ≤ 25 V AC | Resistance | ≤ 150 mΩ/m |
| Operating voltage | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires | 300 pF/m |
| Capacity wire / shield | 300 pF/m | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000237 | ETIM 9.0 | EC000237 |
| ETIM 10.0 | EC000237 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 | | |