

**PAC-D9M-D9F-HF-5M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

|            |                                   |
|------------|-----------------------------------|
| Order No.  | 2420580050                        |
| Type       | <a href="#">PAC-D9M-D9F-HF-5M</a> |
| GTIN (EAN) | 4032248415328                     |
| Qty.       | 1 items                           |

## PAC-D9M-D9F-HF-5M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Dimensions and weights

|            |          |
|------------|----------|
| Net weight | 832.62 g |
|------------|----------|

### Temperatures

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

### Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

### General Data

|                     |                 |                       |                      |
|---------------------|-----------------|-----------------------|----------------------|
| Cable length        | 5 m             | Suitable for          | Analogue signals     |
| Interface connector | SUB-D MALE 9P   | Number of poles, min. | 9-pole               |
| Connector PLC side  | SUB-D FEMALE 9P | Wire cross-section    | 0.25 mm <sup>2</sup> |

### Electrical Data

|                        |                     |   |           |
|------------------------|---------------------|---|-----------|
| Total current, max.    | 3 A                 | Permissible current strength per path, max. | 1 A       |
| Rated voltage          | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Operating voltage      | ≤ 60 V DC ≤ 25 V AC | Capacity wire / wires                       | 300 pF/m  |
| Capacity wire / shield | 300 pF/m            |   |           |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |