

**PAC-HE40-HE40-HF-4M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

Order No.	2425960040
Type	<a href="#">PAC-HE40-HE40-HF-4M</a>
GTIN (EAN)	4099986598515
Qty.	1 items

**PAC-HE40-HE40-HF-4M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 596 g

**Temperatures**

Storage temperature -10...60 °C      Operating temperature -10...50 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

**General Data**

Cable length	4 m	Suitable for	Digital signals
Cable	Cable LIHH	Interface connector	FLAT CABLE PLANO HE10 40P
Number of poles, min.	40-pole	Connector PLC side	FLAT CABLE PLANO HE10 40P
Wire cross-section	0.14 mm <sup>2</sup>		

**Electrical Data**

Total current, max.	3 A	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 V DC ≤ 25 V AC	Resistance	≤ 150 mΩ/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Capacity wire / wires	300 pF/m
Capacity wire / shield	300 pF/m		

**Classifications**

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		