Data sheet

PAC-D9F-F-HF-5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

General ordering data

Order No.	2426020050
Type	PAC-D9F-F-HF-5M
GTIN (EAN)	4099986598799
Qty.	1 items

Data sheet

PAC-D9F-F-HF-5M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform

Dimensions and weights

Net weight	782.25 g

Temperatures

Storage temperature	-10...60 °C	Operating temperature	-10...50 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

General Data

Cable length	5 m	Suitable for	Analogue signals
Interface connector	SUB-D FEMALE 9P	Number of poles, min.	9-pole
Connector PLC side	H0.25/10 (FERRULES 0.25mm²)	Wire cross-section	0.25 mm²

Electrical Data

Total current, max.	3 A	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 80 mΩ/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Capacity (wire / wires)	300 pF/m
Capacity (wire / shield)	300 pF/m		

Rated data UL

Total current, max.	3 A

Classifications

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		