

**PAC-D9F-D9F-HF-5M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Similar to illustration

**General ordering data**

Order No.	2426110050
Type	<a href="#">PAC-D9F-D9F-HF-5M</a>
GTIN (EAN)	4099986599352
Qty.	1 items

**PAC-D9F-D9F-HF-5M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Net weight 832.82 g

**Temperatures**

Storage temperature -10...60 °C      Operating temperature -10...50 °C

**Environmental Product Compliance**

RoHS Compliance Status Compliant  
 REACH SVHC No SVHC above 0.1 wt%

**General Data**

Cable length	5 m	Suitable for	Analogue signals
Interface connector	SUB-D FEMALE 9P	Number of poles, min.	9-pole
Connector PLC side	SUB-D FEMALE 9P	Wire cross-section	0.25 mm <sup>2</sup>

**Electrical Data**

Total current, max.	3 A	Permissible current strength per path, max.	1 A
Rated voltage	≤ 60 Vdc ≤ 25 Vac	Resistance	≤ 80 mΩ/m
Operating voltage	≤ 60 V DC ≤ 25 V AC	Capacity wire / wires	300 pF/m
Capacity wire / shield	300 pF/m		

**Classifications**

ETIM 8.0	EC000237	ETIM 9.0	EC000237
ETIM 10.0	EC000237	ECLASS 14.0	27-24-22-20
ECLASS 15.0	27-24-22-20		