

## PAC-D25M-D25F-HF-10M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |                                      |
|------------|--------------------------------------|
|            |                                      |
| Order No.  | 2426160100                           |
| Type       | <a href="#">PAC-D25M-D25F-HF-10M</a> |
| GTIN (EAN) | 4099986599635                        |
| Qty.       | 1 items                              |

**PAC-D25M-D25F-HF-10M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |           |
|------------|-----------|
| Net weight | 1728.39 g |
|------------|-----------|

**Temperatures**

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

**General Data**

|                       |                      |                     |                  |
|-----------------------|----------------------|---------------------|------------------|
| Cable length          | 10 m                 | Suitable for        | Analogue signals |
| Cable                 | Cable LIHCH          | Interface connector | SUB-D MALE 25P   |
| Number of poles, min. | 25-pole              | Connector PLC side  | SUB-D FEMALE 25P |
| Wire cross-section    | 0.25 mm <sup>2</sup> |                     |                  |

**Electrical Data**

|                          |                     |                                             |           |
|--------------------------|---------------------|---------------------------------------------|-----------|
| Total current, max.      | 3 A                 | Permissible current strength per path, max. | 1 A       |
| Rated voltage            | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Operating voltage        | ≤ 60 V DC ≤ 25 V AC | Capacity (wire / wires)                     | 300 pF/m  |
| Capacity (wire / shield) | 300 pF/m            |                                             |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |