

UR67-PN-HP-8IOL-12-30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	Automation Products - u-remote IP67, Sensor-actuator active distributor
Order No.	2426250000
Type	UR67-PN-HP-8IOL-12-30M
GTIN (EAN)	4050118434354
Qty.	1 items

UR67-PN-HP-8IOL-12-30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Dimensions and weights

Net weight	480 g
------------	-------

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	82327f13-cd27-455a-ab5b-a62e1996dcf8

Digital inputs

Overload protection	Yes	
Diagnosis indication	via LED	
Diagnostic display	Per channel, via LED, red	
Status indicator	Per channel, via LED, yellow	
Digital inputs	Short-circuit protection	Yes
	Overload protection	Yes
	Reverse polarity protection	Yes
Input type	P-switching	
Short-circuit protection	Yes	
Number	4	

Digital outputs

Overload protection	Yes	
Diagnosis indication	via LED	
Diagnostic display	Per channel, via LED, red	
Digital outputs	Short-circuit protection	Yes
	Overload protection	Yes
	Reverse polarity protection	Yes
Short-circuit proof	Yes	
Short-circuit protection	Yes	
Output voltage, low	- 1 V	
Status indicator	Per channel, via LED, yellow	
Output voltage, high	max. 2 V	

General data

Housing main material	Zinc diecast	Protection degree	IP67
-----------------------	--------------	-------------------	------

Supply voltage

Reverse polarity protection	Yes	Power consumption of module electronics	160 mA typical
-----------------------------	-----	---	----------------

UR67-PN-HP-8IOL-12-30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Classifications

ETIM 8.0	EC001599	ETIM 9.0	EC001599
ETIM 10.0	EC001599	ECLASS 14.0	27-24-26-04
ECLASS 15.0	27-24-26-04		