

**UR67-MP-HP-16DI-12-60M****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



More performance. Simplified.

u-remote.

Weidmüller u-remote – our innovative remote I/O concept with IP 67 which focuses purely on user benefits: tailored planning, faster installation, safer start-up, no more down-time. For considerably improved performance and greater productivity. u-remote stands for "More Performance". Simplified

**General ordering data**

|            |                                                                                        |
|------------|----------------------------------------------------------------------------------------|
| Version    | Automation Products - u-remote IP67, Sensor-actuator active distributor, PROFINET V2.3 |
| Order No.  | <a href="#">2426270000</a>                                                             |
| Type       | UR67-MP-HP-16DI-12-60M                                                                 |
| GTIN (EAN) | 4050118434422                                                                          |
| Qty.       | 1 items                                                                                |

## UR67-MP-HP-16DI-12-60M

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E141197

## Dimensions and weights

|            |        |                 |              |
|------------|--------|-----------------|--------------|
| Height     | 51 mm  | Height (inches) | 2.0079 inch  |
| Width      | 60 mm  | Width (inches)  | 2.3622 inch  |
| Length     | 255 mm | Length (inches) | 10.0394 inch |
| Net weight | 500 g  |                 |              |

## Environmental Product Compliance

RoHS Compliance Status Compliant with exemption

RoHS Exemption (if applicable/known) 6c

REACH SVHC Lead 7439-92-1

SCIP 82327f13-cd27-455a-ab5b-a62e1996dcf8

## Connections

|                         |                |                          |                |
|-------------------------|----------------|--------------------------|----------------|
| Supply voltage (AUX-IN) | PushPull-Power | Supply voltage (AUX-OUT) | PushPull-Power |
|-------------------------|----------------|--------------------------|----------------|

## Digital inputs

Diagnostic display Per channel, via LED, red

Input current, high Type 1 in acc. with IEC 61131-2

Status indicator Per channel, via LED, yellow

|                |                             |     |
|----------------|-----------------------------|-----|
| Digital inputs | Short-circuit protection    | Yes |
|                | Overload protection         | Yes |
|                | Reverse polarity protection | Yes |

Input current, low Type 1 in acc. with IEC 61131-2

Input voltage, high &gt; 11 V

Input voltage, low &lt;5 V

## General data

|                           |       |                       |              |
|---------------------------|-------|-----------------------|--------------|
| UL 94 flammability rating | UL 94 | Housing main material | Zinc diecast |
| Protection degree         | IP67  |                       |              |

## Supply voltage

|                                         |                |                   |      |
|-----------------------------------------|----------------|-------------------|------|
| Reverse polarity protection             | Yes            | Operating voltage | 24 V |
| Power consumption of module electronics | 100 mA typical |                   |      |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001599    | ETIM 9.0    | EC001599    |
| ETIM 10.0   | EC001599    | ECLASS 14.0 | 27-24-26-04 |
| ECLASS 15.0 | 27-24-26-04 |             |             |