

**HDC MBUS4 D5E MC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

Version	Accessories
Order No.	<a href="#">2427920000</a>
Type	HDC MBUS4 D5E MC
GTIN (EAN)	4050118437119
Qty.	2 items

## HDC MBUS4 D5E MC

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

Depth	34.8 mm	Depth (inches)	1.3701 inch
Height	34.8 mm	Height (inches)	1.3701 inch
Width	12.2 mm	Width (inches)	0.4803 inch
Net weight	8 g		

### Temperatures

Limit temperature -40 °C ... 90 °C

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	2ac5c63f-7f5e-465a-860d-49cfb7bbe5b5

### General data

Number of poles	4	Coding	D-coded
Contact surface	Gold-plated	Transmission rate	100 MBit/s
Insulation resistance	≥ 100 MΩ	Category	Cat. 5e
Nominal voltage	250 V	Nominal current	4 A
Plugging cycles	100	Type	Pin
Pollution severity	2		

### Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-18
ECLASS 15.0	27-44-02-18		