



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

General ordering data

Version	Screwdriver insert
Order No.	2433230000
Type	WB IK SL PZ1
GTIN (EAN)	4050118443806
Qty.	1 items

Technical data

Dimensions and weights

Depth	7 mm	Depth (inches)	0.2756 inch
Height	75 mm	Height (inches)	2.9527 inch
Width	7 mm	Width (inches)	0.2756 inch
Net weight	7.04 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE insulated interchangeable bit for crosshead screws, Pozidrive, size 1
------------------------	---

Screwing tools

Blade width (B)	1 mm	Blade thickness (A)	1 mm
Form	Pozidrive	Size	1
Blade length	25 mm	Blade size, crosshead	1
Torque setting, max.	3.8 Nm		

Classifications

ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 14.0	21-04-42-03
ECLASS 15.0	21-04-42-03		